

Visual Inspection



Sterile Visual Flow Indicator

- For High Purity Applications
- Suitable for CIP & SIP
- Eliminates Bacteria Traps



Metaglas® Sight Window

- For Flush Mount Systems
- Eliminates Catastrophic Glass Failure
- Clamp or Bolt Style
- USP Type I Glass



High Pressure In-Line

- Sanitary Visual Flow Indicator
- Metaglas® Safety Windows
- Suitable for CIP & SIP



Metaglas® MetaClamp® Sanitary SightGlass

- Simple
- Low Maintenance
- Indestructible
- USP Class VI Biocompatible
- USP Type I Glass



Hygienic Bubble Trap

- Efficiently Remove Unwanted Gas
- Eliminate Product Contamination
- Self Draining Interior & Exterior

Illumination & Camera Systems



Lumi-View Fiber Optic Light

- Perfect for Light/Sight Port Combinations
- Rigid Bundle Supports Light
- Cool Light Output
- NEMA 4X & IP 65



Lumiglas Vessel Light

- For Hygienic Connections
- Illuminates Vessels Easily & Effectively
- Fits Standard Sanitary Connections



MetaClamp® LED Ring Light

- Hygienic Clamp Connection
- Light/Sight on One Port
- Up to 399 lumens
- Continuous Operation
- Impact, Vibration Resistant
- Cool White Light Output



LumiStar3000 LED Light

- Ultra-Bright 3000 Lumens
- Four Mode Smart Design
- Long ServiceLife
- Impact, Vibration Resistant
- Low Energy Consumption
- NEMA 4X & IP65



Hygienic Camera System

- Remote Monitoring of Process
- Mounts to Hygienic Connections
- High Color Resolution
- EX Version Available

Hygienic Clamps & Fittings



Precision Hygienic Clamp

- Full 316 SS Construction
- High Quality
- Precision Fit




Hygienic Lock-out Clamp

- Full 316 SS Construction
- For Maximum Joint Security



Hygienic Safety Clamp

- Full 316 SS Construction
- Perfect for High Vibration/Steam Cycling Applications



ASME Code Clamp

- Designed to ASME Section VIII Appendix 24
- Sizes 1" - 12"



TCI ClampConnect Fitting

- Flush-Mount Design with Clamp Fastener
- Sizes 1/2" - 8"

L.J. Star...Simple to do Business with

PO Box 1116 • Twinsburg, OH 44087

Applications Engineering Department: 330 405 3040 • Fax: 330 405 3070 • view@ljstar.com • www.ljstar.com

Data Sheet 00-0021 01/23